

- CO

CO 110



> On/Off/Esc
CO 110


> 가 CO , 10 (.)

> Hold/min/max
Hold 가 , ,
> On/Off/Esc ,


> Hol/min/max CO 가 , / , Hol/min/max
> Hol/min/max , / , Hol/min/max
> On/Off/Esc / ,

CO MAX


- > OK
 - CO MAX
 - Select
 - OK
 - START
 - OK
- 가가 CO MAX




- > Select
- UNIT
- 가
- OK
- UNIT
- 가
- Select
- 가 : °C or °F.
- OK
- UNIT
- 가
- On/Off/Esc



- > AUTO OFF
- 가
- AUTO OFF
- 가 OK
- Select
- 가 : 15, 30, 45, 60, 75, 90, 105, 120, OFF
- OK
- AUTO OFF
- 가
- On/Off/Esc



- > Select
- > OK
- > OFF ON
- > Select
- > BEEP
- > On/Off/Esc



- > Select
- > OK
- > Select
- > On/Off/Hold
- > AL 1
- > On/Off/Esc
- > Select

- > [Sun icon]
- > [Sun icon]

- > AAA LR03 1.5 V.



Once returned to KIMO, required waste collection will be assured in the respect of the environment in accordance to 2002/96/CE guidelines relating to WEEE

www.kimo.fr

EXPORT DEPARTMENT
Boulevard de Beaubourg - Emerainville - BP 48
77312 MARNE LA VALLEE CEDEX 2
Tel : + 33.1.60.06.69.25 - Fax : + 33.1.60.06.69.29

